

Fluke 80K-15 High Voltage Probe



Klíčové vlastnosti

- **Voltage range:** 0 to 15kV DC or peak AC, 10kV rms AC
- **Basic accuracy:** DC +/- 2% 60Hz: +/- 5%
- **Division ratio:** 1000:1
- **Safety standards:** IEC 1010-2-031:1993, Type B, 40 kV DC or peak AC, 28kV rms AC, Overvoltage Category I (voltage derived from limited energy transformer).
- **Input resistance:** 1000 Megohm
- **Required meter input resistance:** 10 Megohm

Přehled výrobků: Fluke 80K-15 High Voltage Probe

The 80K-15 is a high voltage probe designed to extend the voltage measuring capability of an AC/DC voltmeter to 15,000 volts peak AC or DC Overvoltage Category I. This means the probe can only be used to make measurements on energy limited circuits within equipment. Examples include high voltage within televisions or photocopy machines. DO NOT use this probe to measure high voltages on power distribution systems. The probe provides high accuracy when used with a voltmeter having 10 Megohm input impedance.

Modely



Fluke 80k 15

Fluke. *Keeping your world up and running.®*

Fluke Europe B.V.
P.O. Box 1186
5602 BD Eindhoven
The Netherlands
Tel: +31 4 0267 5406
E-mail: cee.cs@fluke.com
www.fluke.cz

©2021 Fluke Corporation. Všechna práva vyhrazena.
Případné změny jsou vyhrazeny bez předchozího
upozornění.
12/2021

**Změny tohoto dokumentu nejsou povoleny bez
písemného schválení společnosti Fluke Corporation.**