

# 700BCW Stregkodelæser



## Produktoversigt: 700BCW Stregkodelæser

**Description:** This Hewlett Packard HBSW-8200 Bar Code Wand reads eight common bar code symbologies. Code 39, Interleave 2 or 5, UPC A and E, EAN 8 and 13, Codabar, Code 128, Code 11, Code 93, and MSI Code. Programmable via bar code labels or escape sequences. LED indicates when a bar code has been correctly decoded. Resolution, 0.19 mm. Usable from -20 °C to 65 °C, in ambient light to 100,00 lux. EMI compliance per FCC part 15 Class B. ESD immunity, 25 kV.

**Application:** Supports the scanned entry of procedure identification, tag ID, serial number, and operator ID to a Fluke 743 Documenting Process Calibrator.

## Specifikationer: 700BCW Stregkodelæser

Mechanical and General Specifications	
Size	160 x 23 mm. Coiled cable extends to approximately 2.5 m
Weight	160 g
Warranty	One year
Material	Polycarbonate wand, sapphire tip

## Modeller



### **Fluke 700BCW**

Bar Code Wand

---

Included:

- Bar code wand with integrated decoding circuitry, holder, and users manual
  - Fluke 700BCA Bar Code Adapter
  - Instruction sheet in English, French, German, Italian, and Spanish.
-

**Fluke.** *Keeping your world up and running.®*

**Fluke Danmark A/S**  
c/o Radiometer Medical ApS  
Åkandevej 21  
2700 Brønshøj  
Danmark  
Tlf.: 70 23 58 53  
E-mail: [cs.dk@fluke.com](mailto:cs.dk@fluke.com)  
[www.fluke.dk](http://www.fluke.dk)

©2021 Fluke Corporation. Alle rettigheder  
forbeholdes.  
Oplysningerne kan ændres uden forudgående  
varsel.  
12/2021

**Ændringer i dette dokument er ikke tilladt uden  
skriftlig tilladelse fra Fluke Corporation.**