

Tekniske data

PM9091/001 Koaksialt BNC-kabelsæt, farvekodet, 3 stk, 1,5 m hver




Nøglefunktioner

- Cable length is 1.5 m
- Maximum Signal Voltage: 300 V rms
- Maximum Voltage to Ground: 600 V rms. CAT III per IEC 61010-031
- BB120 Shielded Banana to BNC Adapter is required to adapt to ScopeMeter 120 Series shielded banana jack inputs

Produktoversigt: PM9091/001 Koaksialt BNC-kabelsæt, farvekodet, 3 stk, 1,5 m hver

Each set consists of three black cables with colored BNC male connectors (red, gray and black) for easy identification.

Modeller



Fluke PM9091

50 Ohm Coaxial BNC cable set (3 x 1.5m)

Fluke. *Keeping your world up and running.®*

Fluke Danmark A/S
c/o Radiometer Medical ApS
Åkandevej 21
2700 Brønshøj
Danmark
Tlf.: 70 23 58 53
E-mail: cs.dk@fluke.com
www.fluke.dk

©2021 Fluke Corporation. Alle rettigheder
forbeholdes.
Oplysningerne kan ændres uden forudgående
varsel.
12/2021

**Ændringer i dette dokument er ikke tilladt uden
skriftlig tilladelse fra Fluke Corporation.**