

Tekniske data

Fluke i17XX-flex1500/4pk iFlex® Current Clamps



Produktoversigt: Fluke i17XX-flex1500/4pk iFlex® Current Clamps

The Fluke 17XX 12 inch iFlex flexible current probes measure to 1500A AC while providing the ultimate measurement flexibility. The iFlex probes connect directly to the 173X Energy or Power Logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. Fluke 17XX iFlex cables are available in 12, 24, and 36 inch models.

Modeller



i17XX-flex1500/4pk

1500A 12 inch, 4 pack iFlex® Current Clamps

Fluke. *Keeping your world up and running.®*

Fluke Danmark A/S
c/o Radiometer Medical ApS
Åkandevvej 21
2700 Brønshøj
Danmark
Tlf.: 70 23 58 53
E-mail: cs.dk@fluke.com
www.fluke.dk

©2022 Fluke Corporation. Alle rettigheder
forbeholdes.
Oplysningerne kan ændres uden forudgående
varsel.
01/2022

**Ændringer i dette dokument er ikke tilladt uden
skriftlig tilladelse fra Fluke Corporation.**