


Tekniske data

Fluke 71X Hose Kit Accessory



Produktoversigt: Fluke 71X Hose Kit Accessory

The Fluke 71X Hose Kit is compatible with the 717 and 718 calibrators 100 PSI and below.

Application: Translucent accessory hoses allow the technician to easily identify if there is oil or other contaminants in the hose before they get into your calibrator.

Included: The kit contains three translucent hoses one meter long, easy to connect push fit connectors for both connection to the calibrator and the device under test, and one 1/8 to 1/4 NPT female-female adapter.

Modeller



Fluke 71X

Hose Kit Accessory

Fluke. *Keeping your world up and running.®*

Fluke Danmark A/S
c/o Radiometer Medical ApS
Åkandevej 21
2700 Brønshøj
Danmark
Tlf.: 70 23 58 53
E-mail: cs.dk@fluke.com
www.fluke.dk

©2021 Fluke Corporation. Alle rettigheder
forbeholdes.
Oplysningerne kan ændres uden forudgående
varsel.
12/2021

**Ændringer i dette dokument er ikke tilladt uden
skriftlig tilladelse fra Fluke Corporation.**