


Secondary PRT with Calibration Options - 5608 and 5609



Wichtigste Merkmale

- 5608: -200 °C to 500 °C (80 mm minimum immersion)
- 5609: -200 °C to 670 °C (100 mm minimum immersion)
- ± 0.01 short-term stability
- Calibration not included, NVLAP-accredited calibration optional, lab code 200348-0
- Dry-well reference with 90 ° bend

Produktübersicht: Secondary PRT with Calibration Options - 5608 and 5609

The 5608 comes with a one-eighth inch (3.18 mm) diameter sheath in lengths of 9 inches or 12 inches. The 5609 comes with a one-quarter inch (6.35 mm) diameter sheath in lengths of 12 inches, 15 inches, and 20 inches; or with a 6 mm diameter in lengths of 300 mm, 400 mm, or 500 mm.

When looking for improved response time and reduced stem effect in shallow immersion, look for small diameter probes, because the measurement error called stem effect is caused by the diameter of the stem rather than the length of the stem.

Both of these probes have Inconel™ sheaths and are made using a special manufacturing process, giving them great precision over a wide temperature range. The sensors for these probes are reference-grade platinum and feature four-wire

connections with less noisy measurements than two-wire counterparts.

As standard, each probe includes its resistance value at the triple point of water. If calibration is desired, you can order a NVLAP-accredited calibration from our laboratory; lab code 200348-0. On the report of calibration, you'll get the test data and the ITS90 calibration coefficients that you can easily input into any Fluke Calibration thermometer. If you order your probe with an smart connector, we'll program the coefficients directly into your connector, which loads the coefficients for you when you plug it into our [1524 Handheld Thermometer](#).

Technische Daten: Secondary PRT with Calibration Options - 5608 and 5609

Specifications	
Temperature range	5608: -200 °C to 500 °C
	5609: -200 °C to 670 °C
Nominal resistance at 0.01 °C	100 Ω ± 0.5 Ω
Temperature Coefficient	0.0039250 Ω/Ω/°C
Accuracy ^[1]	See footnote
Short-term repeatability ^[2]	± 0.01 °C at 0.010 °C
	± 0.02 °C at max temp
Drift ^[3]	± 0.01 °C at 0.010 °C
	± 0.02 °C at max temp
Hysteresis	± 0.01 °C maximum
Sensor length	30 mm ± 5 mm (1.2 in ± 0.2 in)
Sensor location	3 mm ± 1 mm from tip (0.1 in ± 0.1 in)
Sheath material	Inconel™ 600
Minimum insulation resistance	5608: 500 MΩ at 23 °C, 20 MΩ at 500 °C
	5609: 500 MΩ at 23 °C, 10 MΩ at 670 °C
Transition junction dimensions	71 mm x 12.5 mm (2.8 in x 0.49 in)
Minimum immersion length ^[4] (<5 mK error)	5608: 80 mm (3.1 in)
	5609: 100 mm (3.9 in)

Maximum immersion length	305 mm (12 in)	
Response time ^[5]	5608:	9 seconds typical
	5609:	12 seconds typical
Self heating (in 0 °C bath)	5608:	75 mW/°C
	5609:	50 mW/°C
Lead-wire cable type	Teflon, [™] 24 AWG	
Lead-wire length	1.8 m (6 ft)	
Lead-wire temperature range	-50 °C to 250 °C	
Calibration	Calibration not included; NVLAP-accredited calibration optional, lab code 200348-0. Please see calibration uncertainty table and its explanation of changeable uncertainties.	

Fluke. *Damit Ihre Welt intakt bleibt.*

Fluke Deutschland GmbH

In den Engematten 14

79286 Glottertal

Telefon: 0 69 2 2222 0203

E-Mail: CS.Deutschland-ELEK@Fluke.com

E-Mail: CS.Deutschland-INDS@Fluke.com

www.fluke.de

©2022 Fluke Corporation. Alle Rechte vorbehalten.

Anderungen vorbehalten

01/2022

Technischer Beratung:

Beratung zu Produkteigenschaften, Spezifikationen,

Messgeräte und Anwendungsfragen

Tel.: +49 (0) 7684 8 00 95 45

E-Mail: techsupport.dach@fluke.com

**Dieses Dokument darf nicht ohne die schriftliche
Genehmigung der Fluke Corporation geändert
werden.**