

TECHNICAL DATA

Fluke EI-162BN 320 mm Diameter Split Core Transformer



Key features

External dimensions (LxWxD): 46 x 36 x 16 cm (20.5 x 16 x 17.2 in)

Weight: 8 kg (17.6 lbs)

Product overview: Fluke EI-162BN 320 mm Diameter Split Core Transformer

Used as a Selective clamp for ground loop resistance measurement around power pylons. Inner diameter of the clamp is 320 mm (12.6 in). Includes the split core transformer. This Split Core Transformer can be used in conjunction with the 1625 Kit or the 1623 Kit.

If non-kit version is owned, the GEOX Probe Cable must be purchased separately.

Ordering information



Fluke EI 162BN

320 mm Diameter Split Core Transformer

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

Fluke Australia
Unit 26, 7 Anella Ave
Castle Hill, NSW 2154 Australia
Phone: 61 2 8850-3333
www.fluke.com.au

©2021 Fluke Corporation. All rights reserved.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**