

TECHNICAL DATA

## Fluke i1730-flex1500 iFlex® Current Clamp



### Product overview: Fluke i1730-flex1500 iFlex® Current Clamp

The Fluke 1730 Energy Logger 12 inch iFlex flexible current probes measure to 1500A AC while providing the ultimate measurement flexibility. The iFlex probes connect directly to the energy logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. Fluke 1730 Energy Logger iFlex cables are available in 12, 24, and 36 inch models.

## Ordering information



### **Fluke i1730-flex1500**

A 12 inch Current Clamp

---

1500A 12 inch

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**Fluke Australia**  
Unit 26, 7 Anella Ave  
Castle Hill, NSW 2154 Australia  
Phone: 61 2 8850-3333  
[www.fluke.com.au](http://www.fluke.com.au)

©2021 Fluke Corporation. All rights reserved.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**