

TECHNICAL DATA

Fluke i1730-flex3000/3pk iFlex® Current Clamps



Product overview: Fluke i1730-flex3000/3pk iFlex® Current Clamps

The Fluke 1730 Energy Logger 24 inch iFlex® flexible current probes expand the measurement range of the Fluke 1730 to 3000 A ac while providing the ultimate measurement flexibility. The iFlex® probes connect directly to the energy logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. Fluke 1730 Energy Logger iFlex® cables are available in 12, 24, and 36 inch.

Ordering information



Fluke i1730-flex3000/3pk

A 24 inch, 3 pack Current Clamps

-
- 3000A 24 inch, 3 pack iFlex® Current Clamps
-

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

Fluke Australia
Unit 26, 7 Anella Ave
Castle Hill, NSW 2154 Australia
Phone: 61 2 8850-3333
www.fluke.com.au

©2021 Fluke Corporation. All rights reserved.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**