


TECHNICAL DATA

Fluke 71X Hose Kit Accessory



Product overview: Fluke 71X Hose Kit Accessory

The Fluke 71X Hose Kit is compatible with the 717 and 718 calibrators 100 PSI and below.

Application: Translucent accessory hoses allow the technician to easily identify if there is oil or other contaminants in the hose before they get into your calibrator.

Included: The kit contains three translucent hoses one meter long, easy to connect push fit connectors for both connection to the calibrator and the device under test, and one 1/8 to 1/4 NPT female-female adapter.

Ordering information



Fluke 71X

Hose Kit Accessory

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

Fluke Australia
Unit 26, 7 Anella Ave
Castle Hill, NSW 2154 Australia
Phone: 61 2 8850-3333
www.fluke.com.au

©2021 Fluke Corporation. All rights reserved.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**