

TECHNICAL DATA

Fluke HC120 Hook Clips (Set of 2: Red, Gray)



Product overview: Fluke HC120 Hook Clips (Set of 2: Red, Gray)

Set of two (one red, one gray) Hook Clips, designed for use with STL 120 Shielded Test Leads, VPS40 and TL75 Test Leads. Accepts wires up to 2.5 mm. The contact material is made of reinforced nickel plated steel

Specifications: Fluke HC120 Hook Clips (Set of 2: Red, Gray)

General Specifications	
Maximum voltage	600 V rms. CAT III per IEC 1010-2-031
Maximum wire size	2.5 mm
Contact material	Nickel plated steel

Ordering information



Fluke HC120

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

Fluke Australia
Unit 26, 7 Anella Ave
Castle Hill, NSW 2154 Australia
Phone: 61 2 8850-3333
www.fluke.com.au

©2021 Fluke Corporation. All rights reserved.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**