


Fluke 8.5 MM Scope with 1 M UV Videoscope Probe



Key features

Optional 1 meter long, 8.5 millimeter Ultraviolet videoscope probe with forward view camera. Compatible with Fluke DS701 and Fluke DS703 FC Videoscopes. Supports all features of the Fluke Videoscopes except Up is Up™

Product overview: Fluke 8.5 MM Scope with 1 M UV Videoscope Probe

Ideal for:

Transportation

- Leaks with smoke and dye
- Structural damage of engine components
- Foreign object debris (FOD) inspection

Oil and Gas

- Wear on pipes and hoses
- Structural damage in pipes and hoses

Energy

- Quality control inspections
- Leak inspections

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

Fluke Australia
Unit 26, 7 Anella Ave
Castle Hill, NSW 2154 Australia
Phone: 61 2 8850-3333
www.fluke.com.au

©2021 Fluke Corporation. All rights reserved.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**