

# Fluke Networks MT-8200-61-TNR IntelliTone™ Pro 200 Tone Generator



## Key features

- Verifies and troubleshoots copper cabling, service and continuity
- Kit includes IntelliTone™ Pro 200 Toner, adapters, patch cables, test leads
- SmartTone analog signals for locating cabling on active networks
- Four distinct cadences for isolating individual wire pairs
- Supports VDV cable types inc. RJ45/11, coax, bare wire

## Product overview: Fluke Networks MT-8200-61-TNR IntelliTone™ Pro 200 Tone Generator

Digital and analog tone generator verifies and troubleshoots copper cabling in networks—identifying the type of service and verifying continuity. F-type connector supports VDV cables: RJ45, RJ11, coaxial, bare wire, banana jacks/test leads. Diagnoses 10/100 Gigabit Ethernet link connectivity with NIC/hub indication.

## Specifications: Fluke Networks MT-8200-61-TNR IntelliTone™ Pro 200 Tone Generator

### General specifications

Operating temperature	32 °F to 104 °F (0 °C to 40 °C)
Storage temperature	-4 °F to +140°F (-20 °C to °C)
Operating relative humidity (% RH without condensation)	95 % (50 °F to 95 °F; 10 °C to 35 °C) 75 % (95 °F to 104 °F; 35 °C to 40 °C) Uncontrolled < 50 °F (< 10 °C)
Vibration	Random, 2 g, 5 Hz-500 Hz
Shock	1 m drop test
Safety	EN 61010-1, Category: None
Altitude	3000 m
EMC	EN 61326-1, FCC Part 15 B
Battery type and life	9 V alkaline (NEDA 1604A or IEC 6LR61); 20 hours typical
Applications	Copper cabling media including; 75 or 50 Ohm Coaxial cable; Two Conductor control, security, generic cabling. 10 Base-T or 10/100 Base-T datacom networks. UTP cable. Shielded Twisted Pair supported in Cable Map function of the IntelliTone 200.

#### Toner specifications

Dimensions	5.54 in x 2.94 in x 1.25 in (14.1 cm x 7.5 cm x 3.2 cm)
Display	LED
Control	Thumbwheel switch
Toner interface	Main Mod8 port for tone generation on all 4 pairs of UTP / STP cabling. F Connector for coaxial cabling Banana Jack Plugs (2) - two conductor wiring
Toner frequency	"IntelliTone™ signal: encoded digital signal Analog SmartTone signal: 500 - 1200Hz, 4 songs"
Output power	5 V p-p
Auto power down	Turns off automatically after 2 1/2 hours of inactivity

## Ordering information



### **MT-8200-61-TNR**

Fluke Networks MT-8200-61-TNR IntelliTone™ Pro 200 Tone Generator

---

Includes:

- IntelliTone™ Pro 200 LAN Toner
  - Coax F connector adapter
  - RJ11 and RJ45 patch cables
  - Test leads with alligator clips
  - Lanyard
  - Quick start guide
  - 9-volt battery
-

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**Fluke Australia**  
Unit 26, 7 Anella Ave  
Castle Hill, NSW 2154 Australia  
Phone: 61 2 8850-3333  
[www.fluke.com.au](http://www.fluke.com.au)

©2021 Fluke Corporation. All rights reserved.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**