

Fluke Networks MicroScanner™ PoE Industrial Ethernet Cable Verifier Kit



Key features

- Perform Cable Testing on Industrial Ethernet Networks (including Ethernet/IP, Profinet, EtherCat based systems)
- Display cable length, wiremap and distance to fault
- Display network switch speeds up to 10G and PoE
- Locate and trace cable with IntelliTone(TM) and Remote ID set
- Report PoE class (0-8)

Product overview: Fluke Networks MicroScanner™ PoE Industrial Ethernet Cable Verifier Kit

The Fluke Networks MicroScanner™ PoE Industrial Ethernet cable verifier performs continuity tests on RJ45, M12X, M12D, and M8D terminated cables in a few seconds and displays results graphically so you can see opens, shorts, and cross wires.

The MS-POE also quickly determines if a problem is caused by insufficient power or the powered device. Cable and power failures result in costly production downtime so it's important to quickly identify where the cable is broken so it can be replaced or repaired.

Includes IntelliTone Pro 200 Probe, Remote ID kit, Duffel Bag, Multi-Connector Adapter, Cat6A patch cord, RJ45 male to RJ45 female patch cord , RJ45/M12X patch cord, RJ45/M12D patch cord, RJ45/M8D patch cord for testing of M12X, M12D, M8D terminated cables.

Specifications: Fluke Networks MicroScanner™ PoE Industrial Ethernet Cable Verifier Kit

Specifications apply at 23 °C (73 °F), unless otherwise noted.

Environmental specifications	
Operating temperature	32 °F to 113 °F (0 °C to 45 °C)
Storage temperature	-4 °F to +140 °F (-20 °C to +60 °C)
Operating relative humidity (% RH without condensation)	90 % (50 °F to 95 °F 10 °C to 35 °C) 75 % (95 °F to 113 °F 35 °C to 45 °C)
Shock and Vibration	Random, 2 g, 5 Hz-500 Hz (Class 2) 1 m drop test with and without wiremap adapter attached
Safety	IEC 61010-1 3rd Edition
Altitude	4,000 m; Storage: 12,000 m
EMC	IEC 61326-1
General specifications	
Test connectors	Shielded 8-pin modular jack accepts 8-pin modular (RJ45) and 4-pin modular (RJ11) plugs.
Power	Battery type: 2 AA (NEDA 15A, IEC LR6) alkaline batteries Battery life: 20 hours of typical use Other compatible battery types: 2 AA photo lithium, NIMH, NICAD
Dimensions and weight (with batteries installed and wiremap adapter attached)	3 in x 6.4in x 1.4 in (7.6 cm x 16.3 cm x 3.6 cm) MicroScanner™ PoE: 10.6 oz (300 g)
Display	Monochrome LCD with backlight
Test modes	
Cable test	Measures length, verifies wiremap, identifies remote ID locators, and detects Ethernet ports. MicroScanner™ PoE also shows HIGH Ω when the resistance of the cable is more than 12.5 Ω . Displays results on one screen.
Tone	Generates IntelliTone™ and normal analog toning signals
PoE	MicroScanner™ PoE: Solicits and detects the presence of 802.3af, at, bt, and UPOE (Cisco's Universal Power over Ethernet) compatible PoE devices
Performance specifications	
Cable types tested	Twisted pair: UTP, FTP, SSTP
Length test	Range: 460 m (1500 ft) Resolution: 0.3 m (1 ft) Typical accuracy: $\pm 4\%$ or 0.6 m (2 ft) whichever is greater. NVP uncertainty is an additional error. Calibration: User-settable NVP for twisted pair. Can determine actual NVP with known length of cable.
Wiremap test	Detects single-wire faults, shorts, miswires, split pairs, and up to seven far-end adapter IDs. The wiremap is drawn with proportional length to visually indicate the approximate location of faults.
Ethernet port detection	MicroScanner™ PoE: Detects the advertised speed of 802.3 Ethernet ports with speeds of 10 Mbps, 100 Mbps, 1 Gbps, 2.5 Gbps, 5 Gbps, and 10 Gbps.

Tone generator

Supports toning and cable mapping with a Fluke Networks digital IntelliTone™ probe. Generates four tones compatible with typical analog probes. SmartTone™ feature gives positive identification of cables in bundles when using an IntelliTone or an analog probe.

Ordering information



MS-POE-IE-KIT

MS-POE-IE-KIT Cable Verifier Kit

Includes:

- MicroScanner™ PoE Industrial Ethernet Professional Kit with IntelliTone Pro 200 Probe
- Remote ID kit
- Duffle Bag
- Multi-Connector Adapter
- Cat6A patch cord
- RJ45 male to RJ45 female patch cord
- RJ45/M12X patch cord
- RJ45/M12D patch cord
- RJ45/M8D patch cord for testing of M12X
- M12D
- M8D terminated cables

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

Fluke Australia
Unit 26, 7 Anella Ave
Castle Hill, NSW 2154 Australia
Phone: 61 2 8850-3333
www.fluke.com.au

©2021 Fluke Corporation. All rights reserved.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**