

## TECHNICAL DATA

# Fluke 787CAL Calibration Module

## Key features

**Application:** The calibration module provides a 9 volt dc supply to the 787. At the same time, it facilitates RS232 communication from the PC running MET/CAL to the 787 over the battery leads of the 787.

## Product overview: Fluke 787CAL Calibration Module

**Description:** The Fluke 787CAL module permits users and service facilities to perform automated MET/CAL verifications and calibrations of the Fluke 787 ProcessMeter.

**Note:** An installation of MET/CAL Calibration Software plus appropriate calibration hardware must be provided by the user.

## Ordering information

### **Fluke 787CAL**

Fluke 787CAL Calibration Module  
Calibration Module

---

Included:

- A calibration manual
  - MET/CAL procedures
  - An interface module that permits serial communication between a 787 and a PC.
-

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**