

## TECHNICAL DATA

# Fluke C150 Soft Carrying Case



## Key features

- Zippered carrying case with belt loop
- Inner pocket for accessory storage
- Compatible with many Fluke products (see below)

## Product overview: Fluke C150 Soft Carrying Case

Organize your Fluke tools and accessories with the C150 Soft Carrying Case featuring a deep zippered case. Inside is an additional pocket to store test leads or small accessories. The exterior is made with a durable, high-quality polyester. The C150 also includes a belt loop so you can always easily grab, go, and keep your tools with you. The case is also compatible with a variety of Fluke tools and clamp meters, including:

- [Fluke 325](#)
- [Fluke 376 FC](#)
- [Fluke 323](#)
- [Fluke 375 FC](#)
- [Fluke T5-1000](#)
- [Fluke 9040](#)

## Specifications: Fluke C150 Soft Carrying Case

Dimensions:

298 x 114 x 56 mm

11.75 x 4.5 x 2.2 in

## Ordering information



**Fluke C150**

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**