

TECHNICAL DATA

Fluke CXT170 Extreme Case



Key features

- Buoyancy allows case to float in salt water with 3.6 kg (7.94 lb) load
- Includes an automatic purge valve for quick equalization after changes in atmospheric pressure
- Features an exclusive 6.4 mm (0.25 in) neoprene O-ring and ABS latches for excellent seal

Product overview: Fluke CXT170 Extreme Case

Unbreakable, watertight, airtight, dustproof, chemical resistant and corrosion proof.

Ordering information



Fluke CXT170

For use with the following test tools:

- Air Quality: 922
 - Insulation Testers: 1503, 1507, 1577, 1587
 - Multimeters: 77 III, 77 IV, 114, 115, 116, 117, 177, 179
 - Process Tools: 712, 714, 715, 717, 718, 787
 - Temperature: 51, 51-2, 52, 52-2, 53, 53-2, 54, 54-2
-

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**