

TECHNICAL DATA

Fluke CXT170 Extreme Case



Key features

- Buoyancy allows case to float in salt water with 3.6 kg (7.94 lb) load
- Includes an automatic purge valve for quick equalization after changes in atmospheric pressure
- Features an exclusive 6.4 mm (0.25 in) neoprene O-ring and ABS latches for excellent seal

Product overview: Fluke CXT170 Extreme Case

Unbreakable, watertight, airtight, dustproof, chemical resistant and corrosion proof.

Ordering information



Fluke CXT170

For use with the following test tools:

- Air Quality: 922
 - Insulation Testers: 1503, 1507, 1577, 1587
 - Multimeters: 77 III, 77 IV, 114, 115, 116, 117, 177, 179
 - Process Tools: 712, 714, 715, 717, 718, 787
 - Temperature: 51, 51-2, 52, 52-2, 53, 53-2, 54, 54-2
-

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com/en-gb

©2022 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**