

## TECHNICAL DATA

# Fluke 17XX i40s-EL Clamp-on Current Transformers 3 pack



## Product overview: Fluke 17XX i40s-EL Clamp-on Current Transformers 3 pack

The Fluke i40s-EL Current Clamp-on Transformer is used for low current measurement; suitable for making measurements up to 40A, and also measures accurately on 1A and 5A secondary current transformers. The i40s-EL jaw is capable of being clamped on current conductors up to 15mm in diameter.

## Ordering information



### **FLUKE-17XX i40s-EL/3pk**

40A Clamp-on Current Transformer, 3 pack

---

**Fluke.** *Keeping your world up and running.®*

**Fluke (UK) Ltd.**  
52 Hurricane Way  
Norwich, Norfolk  
NR6 6JB  
United Kingdom  
Tel.: +44 (0)20 7942 0708  
E-mail: [cs.uk@fluke.com](mailto:cs.uk@fluke.com)  
[www.fluke.com/en-gb](http://www.fluke.com/en-gb)

©2022 Fluke Corporation. All rights reserved.  
Data subject to alteration without notice.  
01/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**