

TECHNICAL DATA

Fluke EI-1623 Selective/Stakeless Clamp Set



Product overview: Fluke EI-1623 Selective/Stakeless Clamp Set

The Selective/Stakeless clamp set is used along with the Fluke 1623-2 and 1625-2 to perform Selective and Stakeless testing. Selective testing means using one clamp along with earth ground stakes to provide earth ground loop resistance values for one earth ground electrode. Stakeless testing uses both clamps provided to perform earth ground loop resistance measurement without stakes. Both tests have the advantage of providing measurements with no disconnection from the grounding system! Safer and quicker. Already included in the Fluke 1623-2 and 1625-2 kits. Both clamps have a 50.8 mm (2-inch) inner diameter.

Ordering information



Fluke EI-1623

Fluke EI-1623 Selective/Stakeless Clamp Set

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com/en-gb

©2022 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**