

## TECHNICAL DATA

## Fluke i1730-flex1500/3pk iFlex® Current Clamps



### Product overview: Fluke i1730-flex1500/3pk iFlex® Current Clamps

The Fluke 1730 Energy Logger 12 inch iFlex® flexible current probes expand the measurement range of the Fluke 1730 to 1500 A ac while providing the ultimate measurement flexibility. The iFlex® probes connect directly to the energy logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. Fluke 1730 Energy Logger iFlex® cables are available in 12, 24, and 36 inch.

## Ordering information



### **Fluke i1730-flex1500/3pk**

1500A 12 inch, 3 Pack

- 
- 1500A 12 inch, 3 pack iFlex® Current Clamps
-

**Fluke.** *Keeping your world up and running.®*

**Fluke (UK) Ltd.**  
52 Hurricane Way  
Norwich, Norfolk  
NR6 6JB  
United Kingdom  
Tel.: +44 (0)20 7942 0708  
E-mail: [cs.uk@fluke.com](mailto:cs.uk@fluke.com)  
[www.fluke.com/en-gb](http://www.fluke.com/en-gb)

©2022 Fluke Corporation. All rights reserved.  
Data subject to alteration without notice.  
01/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**