

TECHNICAL DATA**PLS WCB10****Product overview: PLS WCB10**

The PLS WCB10 is a metallic rotary wall and ceiling mount for all PLS rotary laser levels. The WCB10 is included with the PLS HV2R and PLS HV2G System and Kit configurations.

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com/en-gb

©2022 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**