

## TECHNICAL DATA

# Fluke 80K-40 High Voltage Probe



## Key features

- A high voltage probe that allows a multimeter to measure up to 40,000V respectively. Intended for low energy applications only
- One year warranty

## Product overview: Fluke 80K-40 High Voltage Probe

The 80K-40 is a high voltage probe designed to extend the voltage measuring capability of an AC/DC voltmeter to 40,000 volts peak AC or DC Overvoltage Category I. This means the probe can only be used to make measurements on energy limited circuits within equipment. Examples include high voltage within televisions or photo copy machines. DO NOT use this probe to measure high voltages on power distribution systems. The probe provides high accuracy when used with a voltmeter having 10 Megohm input impedance.

## Ordering information



**Fluke 80K 40**

---

**Fluke.** *Keeping your world up and running.®*

**Fluke (UK) Ltd.**  
52 Hurricane Way  
Norwich, Norfolk  
NR6 6JB  
United Kingdom  
Tel.: +44 (0)20 7942 0708  
E-mail: [cs.uk@fluke.com](mailto:cs.uk@fluke.com)  
[www.fluke.com/en-gb](http://www.fluke.com/en-gb)

©2021 Fluke Corporation. All rights reserved.  
Data subject to alteration without notice.  
10/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**