

Fluke TL82 Automotive Pin and Socket Adapter Set



Product overview: Fluke TL82 Automotive Pin and Socket Adapter Set

An absolute must-have for work on Asian or European vehicles. This collection of male and female adapters allows you to make firm connection to pin and socket connectors. Useful when making voltage, frequency, duty cycle or resistance measurements and a must when measuring current requiring the meter be placed in series in the circuit.

Ordering information



Fluke TL82

Fluke TL82 Automotive Pin & Socket Adapter Set
Automotive Pin & Socket Adapter Set

Set contains:

- Retractable shrouded test leads complete set of 8 pin-and-socket adapters with flexible tips; one red and one black in the following sizes:
 - Size 22 contact 0.030 in. (0.76 mm) rated 3 A
 - Size 20 contact 0.040 in. (1.02 mm) rated 3 A
 - Size 16 contact 0.063 in. (1.60 mm) rated 3 A
 - Size 12 contact 0.093 in. (2.36 mm) rated 3 A
- Tested to 60 V DC

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com/en-gb

©2022 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**