

TECHNICAL DATA

Fluke TL940 Mini-Hook Test Leads



Key features

- 1 pair (red, black) of test leads with multi-stacking 4 mm banana plugs and mini-hooks
- Mini-hooks attach to component leads up to 1.5 mm diameter
- 90 cm long PVC insulated leads
- 30 V rms or 60 V DC, 3 A
- One year warranty

Ordering information



Fluke TL940

Mini-Hook Test Leads

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com/en-gb

©2022 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**