


TECHNICAL DATA

Fluke 8.5 MM Scope with 3 M Videoscope Probe



Key features

Optional 3 meter long, 8.5 millimeter videoscope probe with dual view camera. Compatible with Fluke DS701 and Fluke DS703 FC Videoscopes. Supports all features of the Fluke Videoscopes except Up is Up™

Product overview: Fluke 8.5 MM Scope with 3 M Videoscope Probe

Ideal for:

Light Industrial

- Quality control testing
- Machinery maintenance inspections
- Inspect switches and gears
- Elevator inspections
- Inspect welds

Heavy Duty Equipment

- Inspect hydraulic lines
- Inspect welds

Energy

- Electrical, inspecting runs

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com/en-gb

©2022 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**