

TECHNICAL DATA

FLK-XEthernet 5m Connector**Product overview: FLK-XEthernet 5m Connector**

Gigabit-Ethernet cable with LEMO connector, 5m, for the TiX1000, TiX660 and TiX640 Infrared Cameras.

Ordering information



FLK-XEthernet 5m Connector

For the TiX1000, TiX660 and TiX640 Infrared Cameras.

Fluke. *Keeping your world up and running.*®

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500

BUT. FLUKE SOUTH EAST ASIA PTE LTD
Menera Satu Sentra Kelapa Gading #06-05
JI. Bulevar Kelapa Gading Kav. LA# No. 1
Summarecon Kelapa Gading
Jakarta Utara 14240
Indonesia
Tel: +62 21 2938 5922
Email: info.asean@fluke.com
www.fluke.com/id-en
©2022 Fluke Corporation. Specifications subject to
change without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**