

## TECHNICAL DATA

# Fluke L200 Probe Light



## Key features

- Small, rugged light easily attaches to any Fluke test probe
- Bright white LED illuminates contact area
- Frees both hands for work
- 120 hours of battery life
- Uses 2 3-volt watch batteries

## Ordering information



**Fluke L200**

---

**Fluke.** *Keeping your world up and running.*®

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa  
+31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500

**BUT. FLUKE SOUTH EAST ASIA PTE LTD**  
Menera Satu Sentra Kelapa Gading #06-05  
JI. Bulevar Kelapa Gading Kav. LA# No. 1  
Summarecon Kelapa Gading  
Jakarta Utara 14240  
Indonesia  
Tel: +62 21 2938 5922  
Email: info.asean@fluke.com  
www.fluke.com/id-en  
©2022 Fluke Corporation. Specifications subject to  
change without notice.  
01/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**