

Fluke 700HTP-2 Hydraulic Test Pump



Key features

- Variable size stroke adjustment, allows the user to vary the volume and pressure per stroke
- Integral pressure adjustment vernier knob for fine pressure adjustment
- Directly connection to pressure modules consolidates two separate pieces into one when performing pressure calibration and testing
- Two ¼ inch NPT pressure ports, one for reference (pressure module or gauge), one for UUT
- Compatible with optional Fluke-700PRV pressure relief valve designed to protect pressure modules from overpressure damage
- Improved priming
- Improved stroke limiting mechanism

Note: The user must provide a hose with appropriate end fittings to apply pressure from the UUT port to the calibration unit under test such as the Fluke-700HTH-1 hose kit.

Product overview: Fluke 700HTP-2 Hydraulic Test Pump

The Fluke 700HTP-2 is a hand operated hydraulic pressure pump designed to generate calibration pressures up to 10,000 psi/690 bar. Designed for use with Fluke-700 series high pressure modules such as the Fluke-700P09, 700P29, 700P30 and 700P31.

Ideal for calibration when connected to a Fluke high pressure module via the reference port. The 700HTP-2 uses distilled water or mineral-based hydraulic oil as a source for calibration of high pressure input devices such as pressure transmitters



or pressure gauges. Can also be used with Fluke 717 pressure calibrators.

Specifications: Fluke 700HTP-2 Hydraulic Test Pump

Mechanical and General Specifications	
Size (L x W x D)	9.5 x 6.1 x 2.6 in (241 x 155 x 66 mm)
Weight	1.29 lb (.58 kg)
Warranty	One year
Material	Wetted materials: 303 stainless steel, aluminum, polyurethane, PTFE, nitrile, and nylon

Ordering information



Fluke 700HTP 2

Hydraulic Test Pump

- ¼ inch NPT to ¼ inch NPT adapter to connect the reference gauge port on the pump body to the 1/4 NPT female fitting on Fluke 700P29, P30, and P31 pressure modules.
- (2) ¼ inch NPT male to ¼ inch BSP Female adapters
- ¼ inch NPT Tee (installed)
- Instruction sheet

Fluke. *Keeping your world up and running.*®

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500

BUT. FLUKE SOUTH EAST ASIA PTE LTD
Menera Satu Sentra Kelapa Gading #06-05
JI. Bulevar Kelapa Gading Kav. LA# No. 1
Summarecon Kelapa Gading
Jakarta Utara 14240
Indonesia

Tel: +62 21 2938 5922
Email: info.asean@fluke.com
www.fluke.com/id-en

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**