

Fluke Networks Industrial Ethernet DSX CableAnalyzer™ Kit



Key features

- Copper cable certifier for TIA category 5 through 6A, twisted-pair cabling with touchscreen project management, TIA Level IIIe accuracy, advanced troubleshooting, 8-hour battery life
- Startup Faster & Prevent Downtime - Validate at the Machine Builder and again when commissioning the machine at the Plant and find marginal cables before they become a problem
- Speed Troubleshooting - Avoid wasting time installing unnecessary bypass cables
- Pass/Fail indication in 10 seconds with full measurement details
- Supports RJ45 and M12D and M12X connectors
- Works on cables running EtherNet/IP™, Profnet™, ModBus TCP™, EtherCAT and other protocols
- Validate Cable Performance to Standards for Industrial Premises (TIA 1005-A, ISO 11801:3) Document test results with LinkWare software

Product overview: Fluke Networks Industrial Ethernet DSX CableAnalyzer™ Kit

Studies show half of Industrial Ethernet problems are caused by cabling. The DSX Industrial Ethernet Kit allows industrial companies & machine builders to validate cable installations to ensure they comply with international standards thereby reducing machine start-up time, & production down time.

Specifications: Fluke Networks Industrial Ethernet DSX CableAnalyzer™ Kit

Cable types	
Shielded and unshielded pair LAN cabling	TIA Category 3, 4, 5, 5e, 6, 6A, 8: 100 Ω ISO/IEC Class C, D, E, E _A , F, F _A and I/II: 100 Ω and 120 Ω
Standard link interface adapters	
Permanent link adapters	Plug type: shielded RJ45 Optional Plug type: Tera
Channel Adapters	Jack type: shielded RJ45 Optional Jack type: Tera, GG45
Test standards	
TIA	Category 3, 4, 5, 5e, 6, 6A, 8 per TIA 568-C.2
ISO/IEC	Class C and D, E, E _A , F, F _A and I/II certification per ISO/IEC
Maximum frequency	DSX-5000: 1000 MHz
General specifications	
Speed of Autotest	DSX-5000: Full 2-way Autotest of Category 5e or 6/Class D or E: 9 seconds. Full 2-way Autotest of Category 6A/Class E _A : 10 seconds
Supported test parameters (The selected test standard determines the test parameters and the frequency range of the tests)	Wire Map, Length, Propagation Delay, Delay Skew, DC Loop Resistance, Pair-to-Pair Resistance Unbalance, Pair Resistance Unbalance, Insertion Loss (Attenuation), Return Loss (RL), Common Mode Return loss (CMRL), Near End Crosstalk (NEXT), Far End Crosstalk (FEXT), Attenuation-to-crosstalk Ratio (ACR-N), ACR-F (ELFEXT), Power Sum ACR-F (ELFEXT), Power Sum NEXT, Power Sum ACR-N, Power Sum Alien NEXT (PS ANEXT), Power Sum Alien Attenuation NEXT Ratio Far End (PS AACR-F), Common Mode to Differential Mode NEXT (CDNEXT), Transverse Conversion Loss (TCL), Equal Level Transverse Conversion Transfer Loss (ELTCTL)
Input protection	Protected against continuous telco voltages and 100 mA over-current. Occasional ISDN over-voltages will not cause damage
Display	5.7 in LCD display with a projected capacitance touchscreen
Case	High impact plastic with shock absorbing overmold
Dimensions	Main Versiv unit with DSX module and battery installed: 2.625 in x 5.25 in x 11.0 in (6.67 cm x 13.33 cm x 27.94 cm)
Weight	Main Versiv unit with DSX module and battery installed: 3 lbs, 5oz (1.28 kg)
Main unit and remote:	Lithium ion battery pack, 7.2 V
Typical battery life:	8 hours
Charge time*	Tester off: 4 hours to charge from 10 % capacity to 90 % capacity.
Languages supported	English, French, German, Italian, Japanese, Portuguese, Spanish, Chinese, Korean, Russian, Trad Chinese, Czech, Polish, Swedish, Hungarian
Calibration	Service center calibration period is 1 year
Integrated Wi-Fi	Meets IEEE 802.11 a/b/g/n; dual band (2.4 GHz and 5 GHz)
Environmental specifications	

Operating temperature	32°F to 113°F (0°C to 45°C)
Storage temperature	-14°F to +140°F (-10°C to +60°C)
Operating relative humidity	0 % to 90 %, 32°F to 95 °F (0°C to 35°C) 0 % to 70 %, 95°F to 113 °F (35°C to 45°C)
Vibration	Random, 2 g, 5 Hz-500 Hz
Shock	1 m drop test with and without module and adapter
Safety	CSA 22.2 No. 61010, IEC 61010-1 3 rd Edition
Operating altitude	13,123 ft (4,000 m) 10,500 ft (3,200 m) with ac adapter
EMC	EN 61326-1

Performance specifications **

DSX-5000	Category 6A/Class E _A test modes (or lower link categories)	Exceed Level IIIe requirements of TIA 1152 and Level IV of IEC 61935-1.
	Class F _A test modes	Exceed Level V requirements as in the draft 4th edition of IEC 61935-1.

Length of twisted pair cabling¹

	Without remote	With remote
Range	800 m (2600 ft)	150 m (490 ft)
Resolution	0.1 m or 1 ft	0.1 m or 1 ft
Accuracy	± (0.3 m + 2 %); 0 m to 150 m ± (0.3 m + 4 %); 150 m to 800 m	± (0.3 m + 2 %)

Propagation delay

	Without Remote	With Remote
Range	4000 ns	750 ns
Resolution	1 ns	1 ns
Accuracy	± (2 ns + 2 %); 0 ns to 750 ns ± (2 ns + 4 %); 750 ns to 4000 ns	± (2 ns + 2 %)

Delay skew

Range	0 ns to 100 ns
Resolution	1 ns
Accuracy	± 10 ns

DC loop resistance test

Range	0 Ω to 540 Ω
Resolution	0.1 Ω
Accuracy	± (1 Ω + 1 %)
Overload recovery time	Less than 10 minutes to rated accuracy following an overvoltage. Referencing is required after repeated or prolonged overvoltage.

*Available in certain geographies currently



**Applies to accessories in the original product purchase

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

BUT. FLUKE SOUTH EAST ASIA PTE LTD

Menera Satu Sentra Kelapa Gading #06-05

Jl. Bulevar Kelapa Gading Kav. LA# No. 1

Summarecon Kelapa Gading

Jakarta Utara 14240

Indonesia

Tel: +62 21 2938 5922

Email: info.asean@fluke.com

www.fluke.com/id-en

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.