

TECHNICAL DATA

# 572-2 High Temperature Infrared Thermometer



## Key features

- High temperature infrared thermometer that measures from -30°C to 900°C (-22°F to 1652°F)
- Offers an ultra-high 60:1 distance-to-spot ratio with dual laser sighting for fast, accurate targeting
- Features a user-selectable multi-language interface
- Displays the temperature plus MAX, MIN, DIF, AVG temperature
- Provides adjustable emissivity and a predefined emissivity table

## Product overview: 572-2 High Temperature Infrared Thermometer

### Fluke-572-2 High Temperature Infrared Thermometer measures temperatures up to 900°C

The Fluke 572-2 High-Temperature Infrared Thermometer is the ideal tool for high-temperature industrial environments all around the world. Whether you work in power utility, metal refining and smelting, glass, cement or petrochemical environments, the 572-2 offers the rugged performance accuracy you need to get the job done, backed by the most trusted name in test tools. The simple, three-button on-screen menu interface saves time and makes even complex measurements easy. With just a few pushes of a button you can adjust emissivity, start data logging, or turn on and off alarms. The 60:1 distance-to-spot ratio with dual laser sighting helps pinpoint the target fast, making it easier to measure small objects from a long distance.

### Other useful features:

- Audible and visible alarms for rapid detection of high and low temperatures outside the limits
- Stores up to 99 data sets for review and analysis
- Powered by two, standard AA batteries -30-
- Presents infrared and thermocouple temperatures on a bright backlit display

- Is compatible with standard mini-connector K-type thermocouples, including ones you already own and have installed
- Features last reading Hold (20 seconds)

## Specifications: 572-2 High Temperature Infrared Thermometer

Infrared Measurements	
Infrared temperature range	-30°C to 900°C (-22°F to 1652°F)
IR accuracy (calibration geometry with ambient temperature 23°C ± 2°C)	≥ 0°C: ± 1°C or ± 1% of the reading, whichever is greater
	≥ -10°C to < 0°C: ±2°C
	< -10°C: ±3°C
	≥ 32°F: ± 2°F or ± 1% of the reading, whichever is greater
	≥ 14°F to < 32°F: ±4°F
< 14°F: ±6°F	
IR repeatability	±0.5% of reading or ±0.5°C (±1°F), whichever is greater
Display resolution	0.1°C / 0.1°F
Distance: Spot	60:1 (calculated at 90% energy)
Minimum spot size	19 mm
Laser sighting	Offset dual laser, output < 1 mW
Spectral response	8 μm to 14 μm
Response time (95%)	< 500 ms
Emissivity	Digitally adjustable from 0.10 to 1.00 by 0.01 or via built-in table of common materials
Contact Measurements	
K-type thermocouple input temperature range	-270°C to 1372°C (-454°F to 2501°F)
K-type thermocouple input accuracy (with ambient temperature 23°C ± 2°C)	< -40°C: ±(1°C + 0.2° / 1°C)
	≥ -40°C: ±1% or 1°C, whichever is greater
	< -40°F: ±(2°F + 0.2° / 1°F)
	≥ -40°F: ±1% or 2°F, whichever is greater
K-type thermocouple	0.1°C / 0.1°F
K-type thermocouple repeatability	±0.5% of reading or ±0.5°C (±1°F), whichever is greater
Measurement Options	
Hi/Low alarms	Audible and two-color visual
Min/Max/Avg/Dif	Yes
Switchable celsius and fahrenheit	Yes
Backlight	Two levels, normal and extra bright for darker environments
Probe input	K-type thermocouple simultaneous display of probe and IR temperature
Trigger lock	Yes

Data storage	99 points
Display	Dot matrix 98 x 96 pixels with function menus
Communication	USB 2.0
<b>K-Type Thermocouple Specifications</b>	
Measurement range (bead probe)	-40°C to 260°C (-40°F to 500°F)
Accuracy	±1.1°C (±2.0°F) from 0°C to 260°C (32°F to 500°F). Typically within 1.1°C (2.0°F) from -40°C to 0°C (-40°F to 32°F)
Cable length	1 m (40 in) K-type thermocouple cable with standard miniature thermocouple connector and bead termination
<b>General Specifications</b>	
Safety and compliance	IEC 60825-1 FDA Laser Class II IEC 61326-1 CE Complaint CMC # 01120009
Operating temperature	0°C to 50°C (32°F to 122°F)
Storage temperature	-20°C to 60°C (-4°F to 140°F)
Relative humidity	10% to 90% RH non-condensing up to 30°C (86°F)
Operating altitude	2000 meters above mean sea level
Weight	0.322 kg (0.7099 lb)
Power	2 AA batteries
Battery life	8 hours with laser and backlight on; 100 hours with laser and backlight off, at 100% duty cycle (thermometer continuously on)

## Ordering information



### **Fluke 572-2**

Fluke 572-2 High-Temperature Infrared Thermometer

---

Includes:

- K-type thermocouple bead probe
  - Durable hard case
  - USB 2.0 computer interface cable
-

**Fluke.** *Keeping your world up and running.*®

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa  
+31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500

**BUT. FLUKE SOUTH EAST ASIA PTE LTD**  
Menera Satu Sentra Kelapa Gading #06-05  
JI. Bulevar Kelapa Gading Kav. LA# No. 1  
Summarecon Kelapa Gading  
Jakarta Utara 14240  
Indonesia  
Tel: +62 21 2938 5922  
Email: info.asean@fluke.com  
www.fluke.com/id-en  
©2022 Fluke Corporation. Specifications subject to  
change without notice.  
01/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**