

TECHNICAL DATA

# Fluke FOM Fiber Optic Meter



## Product overview: Fluke FOM Fiber Optic Meter

The Fluke Fiber Optic Meter (FOM) helps you test and maintain fiber optic cable without having to buy a whole new meter. Plug the FOM directly into any DMM with a mV dc function and a 10 M $\Omega$  input impedance and quickly and accurately verify fiber optic cable system loss. Light sources and patch cords sold separately.

## Ordering information



### **Fluke FOM**

Fluke FOM Fiber Optic Meter

---

**Fluke.** *Keeping your world up and running.®*

**Fluke (UK) Ltd.**  
52 Hurricane Way  
Norwich, Norfolk  
NR6 6JB  
United Kingdom  
Tel.: +44 (0)20 7942 0708  
E-mail: [cs.uk@fluke.com](mailto:cs.uk@fluke.com)  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation. All rights reserved.  
Data subject to alteration without notice.  
11/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**