

TECHNICAL DATA

Fluke C150 Soft Carrying Case



Key features

- Zippered carrying case with belt loop
- Inner pocket for accessory storage
- Compatible with many Fluke products (see below)

Product overview: Fluke C150 Soft Carrying Case

Organize your Fluke tools and accessories with the C150 Soft Carrying Case featuring a deep zippered case. Inside is an additional pocket to store test leads or small accessories. The exterior is made with a durable, high-quality polyester. The C150 also includes a belt loop so you can always easily grab, go, and keep your tools with you. The case is also compatible with a variety of Fluke tools and clamp meters, including:

- [Fluke 325](#)
- [Fluke 376 FC](#)
- [Fluke 323](#)
- [Fluke 375 FC](#)
- [Fluke T5-1000](#)
- [Fluke 9040](#)

Specifications: Fluke C150 Soft Carrying Case

Dimensions:

298 x 114 x 56 mm

11.75 x 4.5 x 2.2 in

Ordering information



Fluke C150

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com

©2021 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**