

TECHNICAL DATA

Fluke i1730-flex1500 iFlex® Current Clamp



Product overview: Fluke i1730-flex1500 iFlex® Current Clamp

The Fluke 1730 Energy Logger 12 inch iFlex flexible current probes measure to 1500A AC while providing the ultimate measurement flexibility. The iFlex probes connect directly to the energy logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. Fluke 1730 Energy Logger iFlex cables are available in 12, 24, and 36 inch models.

Ordering information



Fluke i1730-flex1500

A 12 inch Current Clamp

1500A 12 inch

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com

©2021 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**