

TECHNICAL DATA

Fluke i1730-flex3000 iFlex® Current Clamp



Product overview: Fluke i1730-flex3000 iFlex® Current Clamp

The Fluke 1730 Energy Logger 24 inch iFlex® flexible current probes expand the measurement range of the Fluke 1730 to 3000A AC while providing the ultimate measurement flexibility. The iFlex® probes connect directly to the energy logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. Fluke 1730 Energy Logger iFlex® cables are available in 12, 24, and 36 inch.

Ordering information



Fluke i1730-flex3000

3000A 24 inch

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com

©2021 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**