


Fluke TPS FLEX 18 Flexible Current Probe



Specifications: Fluke TPS FLEX 18 Flexible Current Probe

General Specifications	
Measuring Range selectable per software	1 A to 100 A
	5 A to 500 A
Peak current for sinusoidal currents	240 A
	1350 A
Intrinsic error	1%
Frequency Range	45 Hz to 3.0 kHz
Operating Voltage	300 V CAT IV
Phase Error	0.5°
Jaw Opening	45 cm length
	2 m cable
Errors in % of measuring range at 23°C ± 2 K; 74°F ± 2 K, for 48 to 65 Hz Phase angle error at nominal current I _{max} maximum current without time limit (for AC and DC shunts)	

Ordering information



Fluke TPS FLEX 18

Flexible Current Probe

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com

©2021 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**