

Fluke 80K-6 High Voltage Probe



Key features

- A high voltage probe that allows a multimeter to measure up to 6,000V. Intended for low energy applications only
- One year warranty

Product overview: Fluke 80K-6 High Voltage Probe

The 80K-6 is a high voltage probe designed to extend the voltage measuring capability of an AC/DC voltmeter to 6000 volts peak AC or DC Overvoltage Category I. This means the probe can only be used to make measurements on energy limited circuits within equipment. Examples include high voltage within televisions or photo copy machines. DO NOT use this probe to measure high voltages on power distribution systems. The probe provides high accuracy when used with a voltmeter having 10 Megohm input impedance.

Ordering information



Fluke 80K 6

Fluke 80K-6 High Voltage Probe

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com

©2021 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**