


TECHNICAL DATA

## Fluke 1730-TL0.1M Test Lead Set



### Product overview: Fluke 1730-TL0.1M Test Lead Set

100 mm test lead for connecting measurement input to the Fluke 1730 Energy Logger.

## Ordering information



### **Fluke 1730-TL0.1M**

1000 V CAT III, straight plug; 0.1 m; silicone; red/black

---

**Fluke.** *Keeping your world up and running.®*

**Fluke (UK) Ltd.**  
52 Hurricane Way  
Norwich, Norfolk  
NR6 6JB  
United Kingdom  
Tel.: +44 (0)20 7942 0708  
E-mail: [cs.uk@fluke.com](mailto:cs.uk@fluke.com)  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation. All rights reserved.  
Data subject to alteration without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**