

TECHNICAL DATA

Fluke 1730-TL2M Test Lead Set



Product overview: Fluke 1730-TL2M Test Lead Set

2 m test lead for connecting measurement input to the Fluke 1730 Energy Logger.

Ordering information



Fluke 1730-TL2M

1000 V CAT III; straight plug; 2 m; PVC red/black

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com

©2021 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**