

TECHNICAL DATA

Fluke SVS-500 Shaft Voltage Measurement Kit



Product overview: Fluke SVS-500 Shaft Voltage Measurement Kit

The Fluke SVS-500 Shaft Voltage Measurement kit is designed for use with the Fluke MDA-500 Series Motor Drive Analyzers, and Fluke 190 Series ScopeMeter® Portable Oscilloscopes. The SVS-500 includes a set of 3 carbon fiber brushes, a probe holder with extension rods, and a magnetic base for securely mounting the measurement probes on the motor while measuring shaft voltage

Ordering information



Fluke SVS-500 Shaft Voltage Measurement Kit

Fluke SVS-500 Shaft Voltage Measurement Kit

- Three carbon fiber shaft voltage brushes
- Two-piece probe extension rod
- Magnetic mounting base

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com

©2021 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**