

## TECHNICAL DATA

# Fluke 3.8 MM Scope with 1 M Videoscope Probe



## Key features

Optional 1 meter long, 3.8 millimeter videoscope probe with forward view camera. Compatible with Fluke DS701 and Fluke DS703 FC Videoscopes. Supports all features of the Fluke Videoscopes except Up is Up™

## Product overview: Fluke 3.8 MM Scope with 1 M Videoscope Probe

Ideal for:

### Transportation

- Leaks with smoke and dye
- Structural damage of engine components
- Foreign object debris (FOD) inspection

### Oil and Gas

- Wear on pipes and hoses
- Structural damage in pipes and hoses

### Energy

- Quality control inspections
- Leak inspections

**Fluke.** *Keeping your world up and running.®*

**Fluke (UK) Ltd.**  
52 Hurricane Way  
Norwich, Norfolk  
NR6 6JB  
United Kingdom  
Tel.: +44 (0)20 7942 0708  
E-mail: [cs.uk@fluke.com](mailto:cs.uk@fluke.com)  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation. All rights reserved.  
Data subject to alteration without notice.  
11/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**