

Smart Infrared 4x Telephoto Lens



Product overview: Smart Infrared 4x Telephoto Lens

View your target magnified 4 times more than a standard lens while staying on the ground or a safe distance away. A 4x telephoto lens can help identify a potential issue in your equipment, even when your target is as tiny and distant as a failed splice on a high electrical line or an overheated refractory on a tall flare stack.

- Avoid the hassle of sending in your camera to calibrate with the lens - with smart lenses you can just attach the lens to any compatible camera and start taking images.
- This lens includes a patent-pending lens attachment system that holds the lens securely in place, reducing lens wobble.
- Made of 100% diamond-turned germanium with an engineered coating, the most efficient available material to transmit energy to the detector.

Compatible with TiX580, TiX501, Ti480 PRO, Ti401 PRO

Specifications: Smart Infrared 4x Telephoto Lens

Description		
IFOV (spatial resolution)	Ti401 PRO / Ti480 PRO	0.17 mRad
	Ti300+	0.34 mRad
	TiX501 / TiX580	0.17 mRad
Field of view	6.0° H x 4.5° V	



Focus distance	1.5 m (approximately 5 ft)
----------------	----------------------------

Ordering information



FLK-LENS/4XTELE2

For use with the TiX580, TiX501, Ti480 PRO, Ti401 PRO Infrared Cameras.

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com

©2021 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**