

TECHNICAL DATA

Fluke Telephoto Infrared Lens



Key features

Field-of-View (FOV) is 8.6° x 6.5°

Product overview: Fluke Telephoto Infrared Lens

Optional, field swappable, telephoto thermal lens allows the user to see and measure the temperature of objects at greater distances, or smaller objects at normal distances.

Ordering information



Fluke Lens/Tele1

Fluke Telephoto Infrared Lens

For use with: Ti32 and TiR32



Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com

©2021 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**