

# 2x Telephoto Infrared Smart Lens



## Product overview: 2x Telephoto Infrared Smart Lens

View your target magnified 2 times more than a standard lens, and reduce the need to enter the danger zone in your plant or to climb a tall ladder to capture the critical infrared details that could indicate your equipment has an issue.

Avoid the hassle of sending in your camera to calibrate with the lens – with smart lenses you can just attach the lens to any compatible camera and start taking images.

Made of 100% diamond-turned germanium with an engineered coating, the most efficient available material to transmit energy to the detector.

Compatible with TiX580, TiX501, Ti480 PRO, Ti401 PRO.

## Specifications: 2x Telephoto Infrared Smart Lens

Description		
IFOV (spatial resolution)	Ti401 PRO / Ti480 PRO	0.33 mRad
	Ti300+	0.66 mRad
	TiX501 / TiX580	0.33 mRad
Field of view	12 ° H x 9 ° V	
Focus distance	45 cm (approximately 18 in)	

## Ordering information



---

### **FLK-LENS/TELE2**

For use with the TiX580, TiX501, Ti480 PRO, and Ti401 PRO Infrared Cameras.

---

**Fluke.** *Keeping your world up and running.®*

**Fluke (UK) Ltd.**  
52 Hurricane Way  
Norwich, Norfolk  
NR6 6JB  
United Kingdom  
Tel.: +44 (0)20 7942 0708  
E-mail: [cs.uk@fluke.com](mailto:cs.uk@fluke.com)  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation. All rights reserved.  
Data subject to alteration without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**