

TECHNICAL DATA

PLS HV2G Rotary Laser Level



Key features

- Accuracy: ≤ 2.2 mm @ 30 m ($\leq 3/32$ in @ 100 ft)
- Laser Axis: Green Horizontal and Vertical
- Working range: ≤ 30 m (100 ft)
- Working range with XLD: ≤ 300 m (1000 ft radius)
- 1-meter drop tested
- IP67 certified protected from dust and immersion in water with a depth of up to 1 m (or 3.3 ft) for up to 30 minutes

Product overview: PLS HV2G Rotary Laser Level

The PLS HV2G green beam rotary lasers are designed for the construction job site, offering a rugged ergonomic design and simplified controls. The HV2G emits a laser line in the horizontal or vertical plane. The HV2G rotary lasers also emit a point from the top when placed in the vertical position. The HV2G lasers are ideal for use by general contractors, electricians, plumbers, and landscapers in both interior and exterior applications.

These professional-grade tools offer the accuracy and durability you can expect from PLS, a Fluke Company.

- The HV2G rotary laser level emits a self-leveling horizontal laser plane and can be used in the vertical position to emit a vertical laser plane. Applications include setting foundations and footings, concrete pours, drywall terracing, contour framing and suspended ceiling installation.
- HV2G comes with metal ceiling and wall bracket to help with large suspended ceiling layout and installation
- The kit includes elevating tripod and 16-foot grade rod.

Specifications: PLS HV2G Rotary Laser Level

Rotary levels	PLS HV2R	PLS HV2G
Laser	Class II red	Class II green
Laser axis	Horizontal and Vertical	Horizontal and vertical
Accuracy	≤ 2.2 mm @ 30 m (≤ 3/32 in @ 100 ft)	≤ 2.2 mm @ 30 m (≤ 3/32 in @ 100 ft)
Auto-leveling range	± 5-degrees	± 5-degrees
Manual slope range	± 5-degrees	± 5-degrees
Working range		
Without XLD laser detector	≤ 30 m (100 ft)	≤ 30 m (100 ft)
With XLD laser detector	≤ 300 m (1000 ft)	≤ 300 m (1000 ft)
Weight	3 kg (6.6 lb)	3 kg (6.6 lb)
Drop test	1 m	1 m
IP rating	IP67	IP67
Operating temperature	-20 °C to 50 °C (-4 °F to 122 °F)	-20 °C to 50 °C (-4 °F to 122 °F)
Battery	4 x D Alkaline or NiMH rechargeable	4 x D Alkaline or NiMH rechargeable
Battery life	> 60 hours	> 60 hours

Accessories	PLS XLD Rotary Laser Detector
Working range	300m (1000 ft)
Dimensions	135 mm x 69 mm x 25 mm
Weight	0.19 kg (0.42 lbs)
Drop test	1 m
IP rating	IP67
Operating temperature	-20 °C to 50 °C (-4 °F to 122 °F)
Battery	1 x AA Alkaline
Battery life	> 50 hours
Visible spectrum	450 nm – 800 nm
Accuracy	
Fine	1 mm (0.05 in)
Medium	2 mm (0.1 in)
Coarse	5 mm (0.2 in)

Electromagnetic compatibility (EMC)

<p>International</p>	<p>IEC 61326-1: Basic Electromagnetic Environment CISPR 11: Group 1, Class B</p> <p>Group 1: Equipment has intentionally generated and/or uses conductively-coupled radio frequency energy that is necessary for the internal function of the equipment itself.</p> <p>Class B: Equipment is suitable for use in domestic establishments and in establishments directly connected to a low voltage power supply network which supplies buildings used for domestic purposes.</p> <p>Emissions that exceed the levels required by CISPR 11 can occur when the equipment is connected to a test object</p>
<p>Korea (KCC)</p>	<p>Class B Equipment (Broadcast communications equipment for home)</p>
<p>USA (FCC)</p>	<p>47 CFR 15 subpart B. This product is considered an exempt device per clause 15.103.</p>

Fluke. *Keeping your world up and running.*®

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com

©2021 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**