

TECHNICAL DATA

PLS XLD**Product overview: PLS XLD**

The PLS XLD is a red and green rotary laser detector for use with all PLS rotary lasers. This accessory comes shipped in a printed cardboard box.

Specifications: PLS XLD

Specifications:

- Range: ≤600 m (2000 ft)
- Battery: 1x AA Alkaline
- Size: 135 mm x 69 mm x 25 mm (5.3 in x 2.7 in x 1.0 in)
- Weight: 0.19 kg (0.42 lb)

Fluke. *Keeping your world up and running.®*

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom
Tel.: +44 (0)20 7942 0708
E-mail: cs.uk@fluke.com
www.fluke.com

©2021 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**