

TECHNICAL DATA

# Fluke 700ILF In-Line Filter



## Key features

The Fluke 700ILF In-line Filter is specifically designed to trap fine particles from atmospheric air, compressed air, and instrument air. It is used with the Fluke 713, 717, or 718 Pressure Calibrators. It can also be used to absorb small quantities of liquid oil and water in droplet form.

## Product overview: Fluke 700ILF In-Line Filter

The Fluke 700ILF can be used to isolate the calibrator from the incidental contact with fluids. Particularly useful with the 718 calibrator to help keep moisture or oils from contaminating the on-board pump.

## Specifications: Fluke 700ILF In-Line Filter

General and Technical Specifications	
Inlet fitting	1/8 in brass female NPT
Outlet fitting	1/8 in brass male NPT
Length	2.125 in
Flange diameter	1.875 in
Housing diameter	1.560 in



Max pressure	100 psi
Max pressure	100 psi
Max flow	10 SCFM
Burst pressure	375 psi
Filtration	1 micron

## Ordering information



### **Fluke 700ILF**

In-line Filter

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**