

## TECHNICAL DATA

# Fluke BP880 BNC to Female Double Stacking Banana Plug



## Key features

- Allows for hands-free testing in controlled voltage environments 500 VRMS maximum
- Banana plug is nickel-plated, beryllium copper for low contact resistance
- The BNC shell is plated for tarnish resistance
- Operating temperature +50 °C (+122 °F) maximum

## Product overview: Fluke BP880 BNC to Female Double Stacking Banana Plug

Converts a BNC scope lead to a dual banana plug for connection to a DMM. Required when adapting a shielded BNC cable, found on high-end low current clamps such as the Fluke 80i-110s, to a DMM.

## Ordering information



### **Fluke BP880**

BNC to Female Double Stacking Banana Plug

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**