

TECHNICAL DATA

Fluke i1730-flex1500 iFlex® Current Clamp



Product overview: Fluke i1730-flex1500 iFlex® Current Clamp

The Fluke 1730 Energy Logger 12 inch iFlex flexible current probes measure to 1500A AC while providing the ultimate measurement flexibility. The iFlex probes connect directly to the energy logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. Fluke 1730 Energy Logger iFlex cables are available in 12, 24, and 36 inch models.

Ordering information



Fluke i1730-flex1500

A 12 inch Current Clamp

1500A 12 inch

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**