

# Fluke 700HTP-2 Hydraulic Test Pump



## Key features

- Variable size stroke adjustment, allows the user to vary the volume and pressure per stroke
- Integral pressure adjustment vernier knob for fine pressure adjustment
- Directly connection to pressure modules consolidates two separate pieces into one when performing pressure calibration and testing
- Two ¼ inch NPT pressure ports, one for reference (pressure module or gauge), one for UUT
- Compatible with optional Fluke-700PRV pressure relief valve designed to protect pressure modules from overpressure damage
- Improved priming
- Improved stroke limiting mechanism

Note: The user must provide a hose with appropriate end fittings to apply pressure from the UUT port to the calibration unit under test such as the Fluke-700HTH-1 hose kit.

## Product overview: Fluke 700HTP-2 Hydraulic Test Pump

The Fluke 700HTP-2 is a hand operated hydraulic pressure pump designed to generate calibration pressures up to 10,000 psi/690 bar. Designed for use with Fluke-700 series high pressure modules such as the Fluke-700P09, 700P29, 700P30 and 700P31.

Ideal for calibration when connected to a Fluke high pressure module via the reference port. The 700HTP-2 uses distilled water or mineral-based hydraulic oil as a source for calibration of high pressure input devices such as pressure transmitters or pressure gauges. Can also be used with Fluke 717 pressure calibrators.



# Specifications: Fluke 700HTP-2 Hydraulic Test Pump

Mechanical and General Specifications	
Size (L x W x D)	9.5 x 6.1 x 2.6 in (241 x 155 x 66 mm)
Weight	1.29 lb (.58 kg)
Warranty	One year
Material	Wetted materials: 303 stainless steel, aluminum, polyurethane, PTFE, nitrile, and nylon

## Ordering information



### **Fluke 700HTP 2**

Hydraulic Test Pump

- 
- ¼ inch NPT to ¼ inch NPT adapter to connect the reference gauge port on the pump body to the 1/4 NPT female fitting on Fluke 700P29, P30, and P31 pressure modules.
  - (2) ¼ inch NPT male to ¼ inch BSP Female adapters
  - ¼ inch NPT Tee (installed)
  - Instruction sheet
-

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**